


I. Electronic Specifications / Mechanical Specifications / Environmental Specifications


Product			STC-POCLC83A-44	STC-POCL83A-44
Electronic Specifications	Imager		1/3" Interline XGA Color Progressive CCD: ICX204AK	1/3" Interline XGA Monochrome Progressive CCD: ICX204AL
	Total Picture Elements		1077 (H) x 788 (V)	
	Active Picture Elements		XGA: 1024 (H) x 768 (V)	
	Chip Size		5.8 (H) x 4.92 (V) mm	
	Cell Size		4.65 (H) x 4.65 (V) μm	
	Scanning System		Progressive	
	Scanning Method		Full Scanning, Partial Full Scanning, ½ Partial Scanning, ¼ Partial Scanning, Variable Partial Scanning	Full Scanning, Partial Full Scanning, ½ Partial Scanning, ¼ Partial Scanning, Variable Partial Scanning, Binning, Binning Partial Scanning, Binning ½ Partial Scanning, Binning ¼ Partial Scanning, Binning Variable Partial Scanning
	Vertical Frequency (Frame Rate)		43.77 Hz	
	Horizontal Frequency		34.84 kHz	
	Pixel Frequency		44.25 MHz	
	S/N Ratio (Standard Deviation)	@ 8bit output	<= 3 Digit (Gain 0 dB)	
		@ 10bit output	<= 10 Digit (Gain 0 dB)	
	Minimum Scene Illumination		0.25 Lux at F1.2	
	Sync. System		Internal / External	
	Video Output		Digital 8 or 10 bit Camera Link (Base Configuration)	
	Tap		1 Tap	
	Shutter Speed		OFF, 1/5 to 1/96,000 sec. (Variable at every H and clock)	
	Gain		0 to 27 dB	
	Gamma		1.0	
	Power Supply	Input Voltage	DC 12V± 10% via Camera Link connector	
		Consumption	Less than 1.8W	
	Trigger Mode		Edge Preset Trigger (V-reset, Non-reset); Pulse Width Trigger (V-reset, Non-reset)	
	Communication		RS232 via Camera Link connector	
Mechanical Specifications	Dimensions		28 (W) x 28 (H) x 29.5 (D) mm (Not including lens mount and the connector) 28 (W) x 28 (H) x 40 (D) mm (Not including connector)	
	Optical Filter		No IR cut filter	
	Optical Center Accuracy		Positional accuracy in H and V directions: +/- 0.31 mm Rotational accuracy of H and V: +/- 2.1 deg.	
	Materials	Case	Front, base, and rear: Aluminum die cast (ADC 12) Cover: Steel sheet covered with zinc	
		Tripod	Polycarbonate ABS	
	Lens Mount		C mount	
	Interface Connector		HR 10A-7R-6PB (Hirose) or equivalent	
	Tripod		Tripod can be attached to 4 plates (4 screws on the bottom plate, 3 screws on the other 3 plates)	
	Weight		Approximately 52g (Camera: 43g, Tripod: 9g)	
Environmental Specifications	Temperature and Humidity	Operational	Temperature: -5 to 50 °C; Relative Humidity: 0 to 85%(No condensation)	
		Storage	Temperature: -30 to 65 °C; Relative Humidity: 0 to 90%(No condensation)	
	Vibration		20Hz to 200Hz to 20Hz (5min./cycle); Acceleration 10G, 3 directions 30 min. each	
	Shock		Acceleration 70G, half amplitude 6ms, 3 directions 3 times each	
	Standard Compliancy		EMS: EN61000-6-2, EMI: EN55011 (Class B)	
	RoHS		RoHS Compliant	

Spectral Sensitivity Characteristics

STC-POCL83A-44



STC-POCLC83A-44



II. Connector Specifications

A. Camera Link Connector: SDR (3M) equivalent

CAUTION: This product is a PoCL type. Therefore, please use this camera with the cable and the frame grabber board for the PoCL model.

B. IO Connector: HR10A-7R-6PB (Hirose) or equivalent. This connector is the input and output signals. Trigger input and sync input/output signals can be assigned through the camera setting communication.


III. Pin Assignment

A. Camera Link Connector

Pin No.	Signal Name	Pin No.	Signal Name
1	+12V	14	GND
2	X0-	15	X0+
3	X1-	16	X1+
4	X2-	17	X2+
5	Xclk-	18	Xclk+
6	X3-	19	X3+
7	SerTC+	20	SerTC-
8	SerTFG-	21	SerTFG+
9	CC1-(TRG)	22	CC1+(TRG)
10	CC2+	23	CC2-
11	CC3-	24	CC3+
12	CC4+	25	CC4-
13	GND	26	+12V

B. Interface Connector

Pin No.	Signal Name	IN / OUT	Voltage		
				Low Voltage	High Voltage
1	GND	IN	0V		
2	I/O – 1	IN / OUT	IN	0 to +0.5V	+2.5 to +5.0V
			OUT	0V	+3.3V
3	I/O – 2	IN / OUT	IN	0 to +0.5V	+2.5 to +5.0V
			OUT	0V	+3.3V
4	I/O - 3	IN / OUT	IN	0 to +0.5V	+2.5 to +5.0V
			OUT	0V	+3.3V
5	TRG OUT	OUT	OUT	0V	+3.3V
6	N.C.				



Note 1: Trigger input signal can be assigned either on Camera Link connector (CC1) or on the No. 2 pin of the IO connector through the camera setting communication.






Note 2: The external sync signals (HD and VD) can be assigned on the following connectors through the camera settings communication.

- Camera Link connector (CC2: HD signal input, CC3: VD signal input) or
- IO connector (No.4: HD signal input / output, No.3: VD signal input / output)

A. Camera Dimensions





B. Tripod Dimensions



Unit: mm

C. Camera with Tripod Dimensions



Unit: MM

Revisions

Rev	Date	Changes	Notes
1.0	2008/12/09	New Document	
1.1	2010/1/07	Update 1. Electronic Specification (Delete Effective Picture Element) 2. Connector Specification (Change “Interface Connector” to “IO connector”)	
1.2	2011/7/12	Update 1. Add the spectral sensitivity characteristics	